

99 Washington Street Melrose, MA 02176 Phone 781-665-1400 Toll Free 1-800-517-8431

Visit us at www.TestEquipmentDepot.com



#### **Accurate Results Anywhere and Anytime You Need Them**

After more than a century of perfecting the art of measurement through our durable weighing products, OHAUS precision is now available in a line of pen meters that provide accurate measurement of pH, oxidation-reduction potential (ORP), conductivity, salinity, and total dissolved solids (TDS). Starter pen meters are the economical option when you are simply looking for meters that will provide accurate measurement with no restriction.

#### **Standard Features Include:**

- Simple Operation in a Slim and Portable Design—Starter pen meters provide what should be expected of a small pen meter: simple, fast, straightforward, no-frills yet highly accurate operation time and time again.
- Durably Constructed to Withstand Wear and Tear Resulting from Repetitive use— With durable plastic housing, a protective cap that safeguards the sensor and an automatic shutdown feature to preserve battery life, the Starter pen meters can endure consistent use in rugged environments.
- Waterproof Housing Protects the Meters in their Working Environment— Equipped with a wrist strap that helps to prevent unintentional dropping, Starter pen meters are constructed with an IP67 waterproof design that can prevent water damage when accidentally dropped into liquid.

## **Starter** Water Analysis Pen Meters

#### **Convenient pH Testing**

Two models with varying resolution and accuracy, ST10 and ST20 offer a convenient way to measure pH, or the relative acidity or alkalinity of a sample at a given temperature. The pH pen meters can be completely operated with just one hand, freeing up your other hand to handle samples.

#### **pH Meters**

Model	ST20	ST10
Range	0.00-14.00 0.0-14.0	
Resolution	0.01pH 0.1pH	
Accuracy	0.05pH	0.1pH
Temperature Range	0.0-99.0 °C	NA
Temperature Compensation	Yes	NA
Display	Dual	Single
Calibration	3 Point	NA
Buffer Group	4.01, 7.00, 10.01	NA
Automatic Shutdown	6 Minutes of Non-Use	6 Minutes of Non-Use
Battery	4 AG13 1.5V 4 AG13 1.5\ Micro Alkaline Batteries Micro Alkaline Ba	
Size/Weight	ht 185 x 45 x 38 mm, 110g 185 x 45 x 38 mm,	



ST10R and ST20R can bring measurement of ORP virtually anywhere the need for measurement of the availability of electrons in a liquid exist. Both models provide almost instantaneous results and the ST20R offers the ability to hold the reading right on the display to provide additional time for data logging.

#### **ORP Meters**

Model	ST20R	ST10R	
Range	-1000mV-1000mV	-1000mV-1000mV	
Resolution	1mV	1mV	
Accuracy	2mV	2mV	
Temperature Range	0.0-99.0 °C	NA	
Temperature Compensation	Yes	NA	
Display	Dual	Single	
Calibration	NA	NA	
Automatic Shutdown	6 Minutes of Non-Use	6 Minutes of Non-Use	
Battery	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries	
Size/Weight	185 x 45 x 38 mm, 110g	, 110g 185 x 45 x 38 mm, 110g	





#### **Small but Productive Conductivity Meters**

Starter pen meters are the choice for basic testing needs of the total ionic concentration within a solution. With six models that can measure within three different conductivity ranges, there is a Starter conductivity meter for every application that requires portable operation and quick results.

## **Conductivity Meters**

Model	ST20C-C	ST20C-B	ST20C-A
Range	0.00-19.99 ms/cm	0-1999 μs/cm	0.0-199.9 μs/cm
Resolution	10 μs/cm	1 μs/cm	0.1 μs/cm
Accuracy	±1.5% FS	±1.5% FS	±1.5% FS
ATC	With Temperature Display	With Temperature Display	With Temperature Display
Display	Dual	Dual	Dual
Automatic Shutdown	6 Minutes of Non-Use	6 Minutes of Non-Use	6 Minutes of Non-Use
Battery	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries
Size/Weight	185 x 45 x 38 mm, 110g	185 x 45 x 38 mm, 110g	185 x 45 x 38 mm, 110g

Model	ST10C-C	ST10C-B	ST10C-A
Range	0.00-19.99 ms/cm	0-1999 μs/cm	0.0-199.9 μs/cm
Resolution	10 μs/cm	1 μs/cm	0.1 μs/cm
Accuracy	±2.5% FS	±2.5% FS	±2.5% FS
ATC	Without Temperature Display	Without Temperature Display	Without Temperature Display
Display	Single	Single	Single
Automatic Shutdown	6 Minutes of Non-use	6 Minutes of Non-Use	6 Minutes of Non-Use
Battery	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries
Size/Weight	185 x 45 x 38 mm, 110g	185 x 45 x 38 mm, 110g	185 x 45 x 38 mm, 110g

#### **Simple Salinity Measurement**

Starter pen meters combine all of the most useful features for measuring salinity, or the dissolved salt content in a liquid medium. With the combination of quality construction and sturdy design, Starter pen meters will provide durable operation in even toughest environments.

#### **Salinity Meters**

Model	ST20S	ST10S	
Range	0.0-80.0 ppt	0.0-10.0 ppt	
Resolution	0.1 ppt	0.1 ppt	
Accuracy	±1.5% FS	±2.5% FS	
ATC	With Temperature Display	Without Temperature Display	
Display	Dual	Single	
Automatic Shutdown	6 Minutes of Non-Use	6 Minutes of Non-Use	
Battery	4 AG13 1.5V Micro Alkaline Batteries	4 AG13 1.5V Micro Alkaline Batteries	
Size/Weight	185 x 45 x 38 mm, 110g	185 x 45 x 38 mm, 110g	





# **Starter** Water Analysis Pen Meters

### **Complete TDS Meters**

When you need reliable and accurate measurement of TDS, the Starter pen meters offer a great value in a portable and compact design. Bring the Starter TDS meter wherever you need to measure the combined content of all organic and inorganic substances in a liquid.

#### **TDS Meters**

Model	ST20T-B	ST20T-A	ST10T-B	ST10T-A
Range	0-1000 mg/L	0.0-100.0 mg/L	0-1000 mg/L	0.0-100.0 mg/L
Resolution	1 mg/L	0.1 mg/L	1 mg/L	0.1 mg/L
Accuracy	±1.5% FS	±1.5% FS	±2.5% FS	±2.5% FS
ATC	With Temperature Display	With Temperature Display	Without Temperature Display	Without Temperature Display
Display	Dual	Dual	Single	Single
Automatic Shutdown	6 Minutes of Non-Use	6 Minutes of Non-Use	6 Minutes of Non-Use	6 Minutes of Non-Use
Battery	4 AG13 1.5V Micro Alkaline Batteries			
Size/Weight	185 x 45 x 38 mm, 110g			



## **Replacement Electrodes**

Item NO	Description	Compatible with
30087992	Electrode pH10 ST	ST10
30087993	Electrode pH20 ST	ST20
30087994	Electrode CT10A ST	ST10C-A, ST10T-A
30087995	Electrode CT10B ST	ST10C-B, ST10T-B
30087996	Electrode CS10C ST	ST10C-C, ST10S
30087997	Electrode CT20A ST	ST20C-A, ST20T-A
30087998	Electrode CT20B ST	ST20C-B, ST20T-B
30087999	Electrode CS20C ST	ST20C-C, ST20S
30088020	Electrode R10 ST	ST10R
30088021	Electrode R20 ST	ST20R

#### Compliance

• Electromagnetic Compatibility: FCC Part 15 Class B; ICES-003 Class B.



99 Washington Street Melrose, MA 02176 Phone 781-665-1400 Toll Free 1-800-517-8431



